

```
# -- Configuration Options for PhyPiDAQ
# -----

DeviceFile: config/VL53LxConfig.yaml # ToF distance sensor

# -- configuration options for Channels
#
ChanNams: ['s'] # names for channels
ChanUnits: ['mm'] # units for channels
ChanColors: [darkblue, sienna] # channel colours in display

# eventually overwrite Channel Limits obtained from device config
ChanLimits:
- [0., 1500.] # chan 0

# -- configuration options for graphical display
#NHistoryPoints: 120 # number of points used in history
buffer
#DisplayModule: DataLogger # history of channel signals
DisplayModule: DataGraphs # text, bar-graph, history and xy-
#
# -- parameters for data taking
#
Interval: 0.1 # logging interval
startActive: true # start in "active" mode
#
# -- configuration options for output to file
DataFile: testfile.csv # file name for output file,
#DataFile: null # null to disable
CSVseparator: ';' # field separator, set to ';' for
German Excel
```